


# SECUREDGE ELIMINAILER-T

**WOOD NAILER ALTERNATIVE** 



#### **DIMENSIONS**

PRODUCT ID. NO.	H DIM	X DIM	L-1 DIM	L-2 DIM	Bar Material
☐ ELI-T-1525	1.5"	2.5"	1.5"	0.75"	.080" Aluminum
ELI-T-1555	1.5"	5.5"	3"	1.5"	.100" Aluminum
ELI-T-3025	3"	2.5"	1.5"	0.75"	.080" Aluminum
ELI-T-3055	3"	5.5"	3"	1.5"	.100" Aluminum
ELI-T-5240	5.2"	4"	1.5"	0.75"	.125" Aluminum
☐ ELI-T-5255	5.2"	5.5"	3"	1.5"	.125" Aluminum

# SUBSTRATE / ADDITIONAL INFO

If substrate is not given, wood fasteners will be provided.

- Metal (\_\_\_\_\_Metal Deck Height in Inches)
- ☐ Existing Wood Nailer
- Masonry
  - Concrete Wall (3000 PSI Concrete
  - CMU Wall (1500 PSI)

### **QUANTITIES**

\_\_\_\_\_ Lineal Feet (12'-0" Lengths)

Number of 3" Insulation Rolls (For 2.5" Flange) (180 FT Per Roll)

Number of 6" Insulation Rolls (For 4" or 5.5" Flange) (180 FT Per Roll)

(Isolation Tape Not Needed for Metal Substrate or Non-Treated Lumber)

## **APPROVALS**





ANSI/SPRI/FM 4435/ES-1

Test Pressures listed in notes

### **NOTES**

- Isolation Tape Required with Masonry and Existing Wood Nailer (Treated Wood):
  - Must use isolation layer between T-Bar and substrate when used with masonry or treated wood.
    - Examples of isolation layers include rubber or plastic strips, peel and stick membrane or

Manufacturer's isolation tape

- Metal Deck (22 ga. or 20 ga. Only):
  - · Must provide Metal Deck Height.
  - Fasteners provided will be Metal Deck Height Plus 1" Min. Substrate must be 22 ga. or greater
- Existing Wood Nailer:
  - 1.5" and 3" Face Heights: 2.5" flange recommended because of standard nailer size
  - 5.2" Face Height: Due to slotted hole location a minimum of a 2x6 nailer must be used
- Product should be installed per provided installation instructions
- ANSI/SPRI/FM 4435/ES-1 Test Pressure up to 1200 psf.

DDD	JECT	
<b>DD</b> ()	11 - ( 1	

Project Name:	
Architect:	-
Roofing Contractor:	_

#### Project Type:

866-458-3537

(Metal-Era)

	By selecting this box yo confirmed that dimensi are correct. All	ou have verified and ions, sizes, and quantities			
	products will be installed in strict accordance with printed instructions.	SHT#_	1	_ of _	1
		DATE:	12,	/06/2	21

Date:	DRN B'
	CIAD D

Carlisle SynTec Systems
Customer Service

DWG #: 15018-25997

REV: C

MM